

LES Water Outlets Testing 2024-2025

Room	Outlets	ID	Aug. 2024	Mitigation Description	Nov. 2024	2nd Mitigaton	Mitigation Re-check	Dec. 2025
122 Kitchen	Sink	LES 1B	1.2					
122 Kitchen	Sink	LES 1C	2.6					
126 Staff Lunchroom	Sink	LES-2A	2.8					
126 Staff Lunchroom	Fountain combo, fountain	LES-2B	<1.0					
126 Staff Lunchroom	Fountain combo, bottle filler	LES-2C	<1.0					
129/131 Instrumental Music	Sink	LES-3	<1.0					
Nurse (between 105 and 106)	Sink	LES-4	5.5	Installed filter	<1.0			
107	Sink	LES-5	<1.0					
108	Sink	LES-6	3.2					
109	Sink	LES-7	1.5					
110	Sink	LES-8	1.2					
151	Sink	LES-9	<1.0					
152	Sink	LES 10	10.9	faucet, lines and shut-offs	9.6	Installed filter	New shutoff on cold only and filter	<1.0
153	Sink	LES 11	6.5	faucet, lines and shut-offs	8.5	Installed filter	New shutoff on cold only and filter	<1.0
Hallway across from 153	Fountain combo, fountain	LES-12A	<1.0					
Hallway across from 153	Fountain combo, bottle filler	LES-12B	<1.0					
154	Sink	LES-13	<1.0					
156	Sink	LES-14	1.4					
157	Sink	LES-15	2.1					
158	Sink	LES-16	3.3					
159	Sink	LES-17	2.2					
111	Sink	LES-18	3.5					
112	Sink	LES-19	3.3					
113	Sink	LES-20	3.8					
114	Sink	LES-21	1.2					
117 Reading	Sink	LES-22	4.8					
121 Cafeteria	Fountain combo, fountain	LES-23A	<1.0					
121 Cafeteria	Fountain combo, bottle filler	LES-23B	<1.0					
Hallway between Library and 403	Fountain/Regular	LES-24	<1.0					
Hallway, near 301	Fountain, combo, fountain	LES-26A	<1.0					
Hallway, near 301	Fountain/Combo, bottle filler	LES-26B	<1.0					
303 PE Office	Sink	LES 27	6.9	faucet and lines	8.7	Pending	Has new faucet, lines and shut-offs	12.4
404	Sink	LES-28	3.4					
405	Sink	LES-29	<1.0					
406	Sink	LES 30	6.3	faucet and lines	5			
407	Sink	LES 31	6.5	Installed filter	10.8	Pending	Has old shut-offs and no filter	<1.0
Hallway, to left of 510	Fountain combo, fountain	LES-32A	<1.0					
Hallway, to left of 510	Fountain combo, bottle filler	LES-32B	<1.0					
505	Sink	LES-33	2.4					
504	Sink	LES-34	<1.0					
503	Sink	LES-35	<1.0					
502	Sink	LES-36	3.8					
501	Sink	LES-37	<1.0					

500	Sink	LES 38	5.3	lines, installed filter	<1.0			
408	Sink	LES-39	<1.0					
409	Sink	LES-40	<1.0					
412	Sink	LES-41	<1.0					